

## Atlantis® abutments implant compatibility chart



Manufacturer	Implant	Atlantis Abutment		Atlantis Crown		Atlantis CustomBase solution - Atlantis Abutment & Atlantis Crown	Atlantis Crown Abutment		Atlantis Conus Abutment	
				Cut-back or Full-contour		Cut-back or Full-contour	Cut-back		Custom	Over-denture
		Titanium Gold-shaded ti	Zirconia	Titanium Gold-shaded ti	Zirconia	Titanium Gold-shaded ti	Titanium	Zirconia	Titanium Gold-shaded ti	Titanium
<b>BioHorizons</b>	<b>INTERNAL</b>									
	Internal 3.5, 4.5, 5.7	x	x	x	x	x	x*	x	x	x*
	Tapered Internal 3.5, 4.5, 5.7	x	x	x	x	x	x*	x	x	x*
	<b>EXTERNAL</b>									
	External implant 3.5	x**							x**	
	External implant 4.0, 5.0	x**	x					x	x**	
<b>Biomet 3i</b>	<b>INTERNAL</b>									
	Certain™ 4/3, 5/4	x	x	x	x	x	x*	x	x	x*
	Certain™ 3.25, 4.0, 5.0, 6.0	x	x	x	x	x	x*	x	x	x*
	Certain™ Prevail™ 3/4/3 (3.4), 4/5/4, 5/6/5, 4/3, 5/4, 6/5	x	x	x	x	x	x*	x	x	x*
	Certain™ XP 4/5, 5/6	x	x	x	x	x	x	x	x	x*
	<b>EXTERNAL</b>									
	Miniplant™ 3.25	x	x					x	x	x
Osseotite™ 3.75, 4.0, 5.0, 6.0	x	x					x	x	x	
	Osseotite™ XP 4/5, 5/6	x	x					x	x	x
<b>Camlog</b>	<b>INTERNAL</b>									
	CONELOG 3.3	x		x		x	x		x	x
	CONELOG 3.8, 4.3	x		x		x	x		x	x
	CONELOG 5.0	x		x		x	x		x	x
	Screw-line Implant 3.3	x		x		x	x		x	x
	Screw-line / Root-line Implant 3.8, 4.3, 5.0, 6.0	x	x	x	x	x	x	x	x	x
<b>Dentsply Sirona</b>	<b>INTERNAL</b>									
	Ankylos® C/X - C/ 3.5, 4.5, 5.5, 7.0 (non-indexed)	x	x	x					x	
	Ankylos® C/X - /X 3.5, 4.5, 5.5, 7.0 (indexed)	x	x	x	x	x			x	x
	OsseoSpeed® EV 3.0 - Green	x		x		x				
	OsseoSpeed® EV 3.6 - Purple	x	x	x	x	x	x	x	x	x
	OsseoSpeed® EV 4.2 - Yellow	x	x	x	x	x	x	x	x	x
	OsseoSpeed® EV 4.8 - Blue	x	x	x	x	x	x	x	x	x
	OsseoSpeed® EV 5.4 - Brown	x	x	x	x	x	x	x	x	x
	OsseoSpeed® Profile EV 4.2 Yellow	x	x	x		x			x	x
	OsseoSpeed® Profile EV 4.8 Blue	x	x	x		x			x	x
	OsseoSpeed®/OsseoSpeed® TX 3.0 - Yellow	x		x		x				
	OsseoSpeed®/OsseoSpeed® TX 3.5, 4.0 - Aqua	x	x	x	x	x		x	x	x
	OsseoSpeed®/OsseoSpeed® TX 4.5, 5.0 - Lilac	x	x	x	x	x		x	x	x
	OsseoSpeed® TX Profile 4.5, 5.0	x		x		x			x	x
	OsseoSpeed® 4.0 - Blue (Previous)	x**							x**	
	Xive® S 3.0	x		x		x				
	Xive® S 3.4, 3.8, 4.5, 5.5	x	x	x	x	x		x	x	x
Frialit™ 3.4, 3.8, 4.5, 5.5	x	x	x	x	x		x	x	x	
<b>Keystone Dental</b>	<b>INTERNAL</b>									
	PrimaConnex™ SD 3.3, 3.5, Genesis™ 3.8	x	x	x	x	x	x	x	x	x
	PrimaConnex™ RD 4.0, 4.1, Genesis™ 4.5	x	x	x	x	x	x	x	x	x
	PrimaConnex™ WD 5.0, Genesis™ 5.5, 6.5	x	x	x	x	x	x	x	x	x

All trademarks and company names are the property of their respective owners.

Please turn over →

\* 2 day extra Turnaround time.

\*\* 3 day extra Turnaround time.

Manufacturer	Implant	Atlantis Abutment		Atlantis Crown		Atlantis CustomBase solution - Atlantis Abutment & Atlantis Crown	Atlantis Crown Abutment		Atlantis Conus Abutment	
				Cut-back or Full-contour		Cut-back or Full-contour	Cut-back		Custom	Over-denture
		Titanium Gold-shaded ti	Zirconia	Titanium Gold-shaded ti	Zirconia	Titanium Gold-shaded ti	Titanium	Zirconia	Titanium Gold-shaded ti	Titanium
Nobel Biocare	<b>INTERNAL</b>									
	NobelActive™ 3.0	x		x		x	x			
	NobelActive™ NP 3.5	x	x	x	x	x	x	x	x	x
	NobelActive™ RP 4.3, 5.0	x	x	x	x	x	x	x	x	x
	NobelReplace™ NP 3.5	x	x	x	x	x	x	x	x	x
	NobelReplace™ RP 4.3	x	x	x	x	x	x	x	x	x
	NobelReplace™ WP 5.0	x	x	x	x	x	x	x	x	x
	NobelReplace™ 6.0	x	x	x	x	x	x	x	x	x
	NobelReplace™ Conical Connection NP 3.5	x	x	x	x	x	x	x	x	x
	NobelReplace™ Conical Connection RP 4.3, 5.0	x	x	x	x	x	x	x	x	x
	<b>EXTERNAL</b>									
Brånemark System™ NP 3.3	x		x		x	x		x	x	
Brånemark System™ RP 3.75, 4.0	x	x	x		x	x	x	x	x	
Brånemark System™ WP 5.0, 5.5	x	x	x		x	x	x	x		
Osstem	<b>INTERNAL</b>									
	Osstem TS Mini 3.5	x	x	x	x	x	x	x	x	x
	Osstem TS Regular 4.0, 4.5, 5.0, 6.0, 7.0	x	x	x	x	x	x	x	x	x
Straumann	<b>INTERNAL</b>									
	Bone Level 3.3 NC (Narrow CrossFit™)	x	x	x	x	x	x	x	x	x
	Bone Level 4.1, 4.8 RC (Regular CrossFit™)	x	x	x	x	x	x	x	x	x
	Standard/Standard Plus 4.8 RN (Regular Neck)	x		x		x	x		x	x
	Standard/Standard Plus 4.8 WN (Wide Neck)	x		x		x	x		x	x
	<b>EXTERNAL</b>									
Standard Plus 3.3 NN (Narrow Neck)	x**							x**		
Zimmer Dental	<b>INTERNAL</b>									
	Tapered Screw-Vent™ 3.5, 4.5, 5.7	x	x	x	x	x	x	x	x	x
	Tapered Screw-Vent™ 3.5, 4.5, 5.7 friction fit	x		x		x	x		x	x
	Screw-Vent™ 3.3, 3.7, 4.5	x	x	x	x	x	x	x	x	x
	Screw-Vent™ 3.3, 3.7, 4.5 friction fit	x		x		x	x		x	x
SwissPlus™ 4.8	x		x		x	x		x	x	

All trademarks and company names are the property of their respective owners.

\* 2 day extra Turnaround time.

\*\* 3 day extra Turnaround time.